




DrsLight2 Curing Light

Multi-Functional Wireless Curing Light,
Fluorescence Light, Transillumination Light,
and Whitening Accelerator.



Peak 405nm and 460nm


100 Sleeves
Included


Charging Base
Included

Polaroid Curing Light Tip's are Optional for an Additional Fee.

Polaroid

Website: polaroidhealth.com

E-Mail: info@polaroidhealth.com

Phone: 1-844-789-5050



Dual Wavelength LED

Can polymerize any kind of material with dual wavelength. (peak 405 and 460nm)



280° Twist Head

Easily maneuver in a patients mouth to help reduce discomfort and arm fatigue with our one of a kind multi functional unit.



Wide Irradiate Area

Can polymerize for wider area with 11mm diameter. Tip saves time and assures full coverage for cures of any size



Timer Mode

Easily select the amount of time you would like the curing light to be active for and even hold it automatically in place with the optional chair arm! (3 to 20 seconds)



Autoclavable Lens

(Patented Autoclavable Silicone Soft Lens) Our soft lens tip helps prevent patient discomfort if accidentally tapped on a tooth as compared to the hard glass light guides used by others



Interchangeable Tips

Our state of the art removable head pop-off feature can be easily removed to incorporate alternate camera heads such as Fluorescence Head, Trans Illumination Head, & Whitening Accelerator Head. (optional)



6 Curing Modes

Featuring 6 curing modes and a soft start that slowly ramps up the power to deliver deep and even cures that are reliable and repeatable. (Low, soft start, high, pulse, Turbo, and Ortho)



Focused Light


Focused LED light increase its performance.



Large Battery Capacity

You can depend on its large capacity Lithium Ion battery to provide all the power you'll need between charges.

Operation voltage	3.7V
Peak wavelength	405nm and 460nm
Measurement	Approx.273 x 45 x 39 mm
Weight	Approx. 114 g
Charger voltage	5V
Charger measurement	Approx.169 x 148 x 89 mm
Charger weight	Approx. 170 g
Battery	Lithium ion battery
Battery voltage	DC 3.7V
Adapter input voltage	AC 100~ 240V
Adapter output voltage	DC 5V 2A



Contact your local **dealer.**